


[Tous les Produits](#) / [Composants Optiques](#) / [Optiques de Polarisation](#) / [Polariseurs Linéaires](#) / [Polariseurs Absorbants \(Dichroïques\)](#) / [Films Polarisants en Polymère](#)

TECHSPEC® Film Polarisant Linéaire à Contraste Élevé (XP42)



- Transmission élevée de la lumière non polarisée de 400 à 700 nm
- Excellent rapport d'extinction 9000:1
- Disponibles en formats de feuilles
- Options [Haute Température](#) également disponibles



Spécifications

Propriétés optiques


Gamme de Longueur d'Onde (nm):

400 - 700

Informations techniques



XP44 – Linear Polarizer



Produits

Dia. (mm)	Dimensions (mm)	Épaisseur (mm)	Substrat	Traitement	Rapport d'Extinction	Numéro de Stock	Prix	Achat
10.00	-	0.19	Polymer Film XP42-18	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-349	€13,39 Prix sur Quantité	20+ In Stock
12.50	-	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-488	€16,48 Prix sur Quantité	4 In Stock
15.00	-	0.19	Polymer Film XP42-18	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-350	€17,51 Prix sur Quantité	20+ In Stock
20.00	-	0.19	Polymer Film XP42-18	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-351	€18,54 Prix sur Quantité	20+ In Stock
25.00	-	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-489	€19,57 Prix sur Quantité	20+ In Stock
30.00	-	0.19	Polymer Film XP42-18	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-352	€20,60 Prix sur Quantité	20+ In Stock
40.00	-	0.19	Polymer Film XP42-18	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-353	€22,66 Prix sur Quantité	20+ In Stock
50.00	-	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-490	€24,72 Prix sur Quantité	8 In Stock
-	50.0 x 50.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-480	€24,72 Prix sur Quantité	Contact
-	100.0 x 100.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-481	€44,29 Prix sur Quantité	20+ In Stock
-	150.0 x 150.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-482	€63,86 Prix sur Quantité	20+ In Stock
-	200.0 x 200.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-483	€108,15 Prix sur Quantité	20+ In Stock

-	250.0 x 250.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-484	€139,05 Prix sur Quantité	20+ In Stock
-	300.0 x 300.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-485	€187,46 Prix sur Quantité	20+ In Stock
-	600.0 x 500.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-486	€272,95 Prix sur Quantité	5 In Stock
-	600.0 x 1000.0	0.22	Polymer Film XP42-18	Pressure Sensitive Adhesive (PSA) one-sided	9000:1	#29-491	€406,85 Prix sur Quantité	1 In Stock
-	600.0 x 1000.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-487	€406,85 Prix sur Quantité	9 In Stock

[#19-017 Fin de Série](#)



Fin de Série

La disponibilité des produits est limitée. Veuillez noter que nous ne pouvons pas accepter des retours. Recevez jusqu'à 80 % de remise sur des produits sélectionnés. Un code de promotion n'est pas nécessaire.

50.00	-	0.77	Polymer Film XP42-75	-	9000:1		€15,40	10 In Stock
-------	---	------	--------------------------------------	---	--------	--	--------	-------------

[#86-188 Fin de Série](#)



Fin de Série

La disponibilité des produits est limitée. Veuillez noter que nous ne pouvons pas accepter des retours. Recevez jusqu'à 80 % de remise sur des produits sélectionnés. Un code de promotion n'est pas nécessaire.

-	150.0 x 150.0	0.77	Polymer Film XP42-75	-	9000:1		€36,00	15 In Stock
---	---------------	------	--------------------------------------	---	--------	--	--------	-------------

10.00	-	0.40	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-354	€13,39 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	---------------------------	-------------------------	---	--------------

12.50	-	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-500	€16,48 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	--------	-------------------------	---	--------------

15.00	-	0.40	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-355	€17,51 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	---------------------------	-------------------------	---	--------------

20.00	-	0.40	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-356	€18,54 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	---------------------------	-------------------------	---	--------------

25.00	-	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-501	€19,57 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	--------	-------------------------	---	--------------

-	25.0 x 25.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-492	€19,57 Prix sur Quantité	20+ In Stock
---	-------------	------	--------------------------------------	---	--------	-------------------------	---	--------------

30.00	-	0.40	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-357	€20,60 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	---------------------------	-------------------------	---	--------------

40.00	-	0.40	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-358	€22,66 Prix sur Quantité	20+ In Stock
-------	---	------	--------------------------------------	---	---------------------------	-------------------------	---	--------------

50.00	-	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-502	€24,72 Prix sur Quantité	20+ In Stock
-	50.0 x 50.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-493	€24,72 Prix sur Quantité	20+ In Stock
-	100.0 x 100.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-494	€44,29 Prix sur Quantité	5 In Stock
-	150.0 x 150.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-495	€63,86 Prix sur Quantité	20+ In Stock
-	200.0 x 200.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-496	€108,15 Prix sur Quantité	12 In Stock
-	300.0 x 300.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-497	€187,46 Prix sur Quantité	5 In Stock
-	600.0 x 450.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-498	€272,95 Prix sur Quantité	9 In Stock
-	600.0 x 900.0	0.40	Polymer Film XP42-40	Uncoated, Protective Film on Both Sides	9000:1	#29-499	€406,85 Prix sur Quantité	9 In Stock
10.00	-	0.72	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-359	€14,42 Prix sur Quantité	20+ In Stock
12.50	-	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-940	€17,51 Prix sur Quantité	20+ In Stock
15.00	-	0.72	Polymer Film XP42-40	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-360	€17,51 Prix sur Quantité	20+ In Stock
20.00	-	0.72	Polymer Film XP42-70	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-361	€19,57 Prix sur Quantité	20+ In Stock
25.00	-	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-941	€20,60 Prix sur Quantité	14 In Stock
30.00	-	0.72	Polymer Film XP42-70	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-362	€22,66 Prix sur Quantité	20+ In Stock

40.00	-	0.72	Polymer Film XP42-70	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-363	€24,72 Prix sur Quantité	20+ In Stock
50.00	-	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-942	€25,75 Prix sur Quantité	20+ In Stock
-	50.0 x 50.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-943	€25,75 Prix sur Quantité	8 In Stock
-	100.0 x 100.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-944	€45,32 Prix sur Quantité	20+ In Stock
-	150.0 x 150.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-945	€65,92 Prix sur Quantité	20+ In Stock
-	200.0 x 200.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-946	€111,24 Prix sur Quantité	3 In Stock
-	250.0 x 250.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-947	€144,20 Prix sur Quantité	7 In Stock
-	300.0 x 300.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-948	€192,61 Prix sur Quantité	13 In Stock
-	600.0 x 450.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-949	€281,19 Prix sur Quantité	5 In Stock
-	600.0 x 900.0	0.72	Polymer Film XP42-70	-	up to 9000:1	#19-950	€406,85 Prix sur Quantité	20+ In Stock
10.00	-	1.02	Polymer Film XP42-100	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-364	€15,45 Prix sur Quantité	20+ In Stock
12.50	-	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-951	€19,57 Prix sur Quantité	20+ In Stock
15.00	-	1.02	Polymer Film XP42-100	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-365	€19,57 Prix sur Quantité	20+ In Stock
20.00	-	1.02	Polymer Film XP42-100	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-366	€21,63 Prix sur Quantité	20+ In Stock
25.00	-	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-952	€21,63 Prix sur Quantité	4 In Stock
30.00	-	1.02	Polymer Film XP42-100	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-367	€23,69 Prix sur Quantité	20+ In Stock

40.00	-	1.02	Polymer Film XP42-100	Uncoated, protective film on both sides	9000:1 (nominal at 555nm)	#71-368	€25,75 Prix sur Quantité	17 In Stock
50.00	-	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-953	€26,78 Prix sur Quantité	20+ In Stock
-	50.0 x 50.0	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-954	€26,78 Prix sur Quantité	20+ In Stock
-	100.0 x 100.0	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-955	€47,38 Prix sur Quantité	20+ In Stock
-	150.0 x 150.0	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-956	€70,04 Prix sur Quantité	20+ In Stock
-	200.0 x 200.0	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-957	€114,33 Prix sur Quantité	5 In Stock
-	25.0 x 25.0	0.19	Polymer Film XP42-18	Uncoated, Protective Film on Both Sides	9000:1	#29-479	€19,57 Prix sur Quantité	14 In Stock
-	300.0 x 300.0	1.02	Polymer Film XP42-100	-	up to 9000:1	#19-958	€199,82 Prix sur Quantité	11 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK
Téléphone: 1-800-363-1992 :
www.edmundoptics.com