

[Tous les Produits](#) / [Composants Optiques](#) / [Filtres Optiques](#) / [Filtres Coupe-Bande](#)

TECHSPEC®

Filtres Multi-Coupe-Bande OD 6 pour Lasers Nd:YAG



- Blocage Profond OD 6
- Transmission Supérieure à 90%
- Large Gamme de Transmission allant de 325 à 1.200 nm
- [Filtres Coupe-Bande OD 4](#) et [Filtres Coupe-Bande OD 6](#) également disponibles

Spécifications

Propriétés physiques et mécaniques

Épaisseur (mm):	3.50 ±0.1	Construction:	Mounted in Black Anodized Ring
Ouverture Utile (%):	>85		


Propriétés optiques

Densité Optique OD:	≥6.0		
Traitement:	Hard Coated	Qualité de Surface:	60-40
Transmission (%):	>80 avg @ 325 - 400nm >90 avg @ 400 - 1200nm	Bande de Transmission (nm):	325 - 1200
Réfectivité à la Longueur d'Onde Centrale CWL (%):	>99.5	Front d'Onde Transmis, RMS:	1λ

Environnement & durabilité

Durabilité:	MIL-C-48497A
--------------------	--------------

Informations techniques



All mounted TECHSPEC® Optical Filters have an arrow on the side of the mount that points to the filter-coated surface for quick reference. Filter oriented such that arrow points to filter coated surface S1. Anti-reflective (AR) coating is applied to S2.

Produits

Dia. (mm)	CWL (nm)	FWHM (nm)	Bande de Transmission (nm)	Numéro de Stock	Prix	Achat
12.50	355.00	10.00	325 - 1200	#87-015	€661,26 Prix sur Quantité	6 In Stock
12.50	532.00	25.00	325 - 1200	#87-017	€661,26 Prix sur Quantité	Contact
25.00	355.00	10.00	325 - 1200	#87-019	€1.059,87 Prix sur Quantité	15 In Stock
25.00	532.00	25.00	325 - 1200	#87-021	€1.059,87 Prix sur Quantité	2 In Stock
50.00	355.00	10.00	325 - 1200	#87-023	€2.264,97 Prix sur Quantité	Contact
50.00	532.00	25.00	325 - 1200	#87-025	€2.264,97 Prix sur Quantité	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Téléphone: 1-800-363-1992 :

www.edmundoptics.com