

[Tous les Produits](#) / [Composants Optiques](#) / [Lentilles Optiques](#) / [Lentilles Spécialisées](#)

Collimateurs Focalisables



- Peuvent être couplés à des fibres optiques câblées standards de NA 0,22
- Options de traitement disponibles pour l'UV-VIS ou le VIS-NIR
- Plusieurs ouvertures et distances focales proposées

Spécifications


Environnement & durabilité

Température d'Utilisation (°C):

-40 to 100


Informations techniques

Fiber with 4mm Aperture Fiber Optic Collimator




The 4mm Aperture Fiber Optic Collimator threads directly onto FC or SMA fiber.

Fiber with 10mm Aperture Fiber Optic Collimator



Each 10mm Aperture Fiber Optic Collimator includes an FC or SMA adapter that is inserted into the collimator and locked by a set screw.

Fiber with 10mm Aperture Fiber Optic Collimator and Refocusing Assembly



A 10mm Aperture Refocusing Assembly can then be directly threaded onto the 10mm Aperture Fiber Optic Collimator.

Produits

Taille d'Ouverture	Connecteur	FL (mm)	Type	Gamme de Longueur d'Onde (nm)	Numéro de Stock	Prix	Achat
4.0	FC	10.00	Fiber Collimator	190 - 1250	#88-189	€235,87 Prix sur Quantité	9 In Stock
4.0	SMA	10.00	Fiber Collimator	190 - 1250	#88-173	€235,87 Prix sur Quantité	9 In Stock
4.0	FC	10.00	Fiber Collimator	350 - 2200	#88-188	€192,61 Prix sur Quantité	2 In Stock
4.0	SMA	10.00	Fiber Collimator	350 - 2200	#88-172	€182,31 Prix sur Quantité	8 In Stock
10.0	FC	18.00	Fiber Collimator	190 - 1250	#88-191	€396,55 Prix sur Quantité	Contact
10.0	SMA	18.00	Fiber Collimator	190 - 1250	#88-181	€396,55 Prix sur Quantité	Contact
10.0	FC	18.00	Fiber Collimator	350 - 2200	#88-190	€235,87 Prix sur Quantité	5 In Stock
10.0	SMA	18.00	Fiber Collimator	350 - 2200	#88-180	€235,87 Prix sur Quantité	1 In Stock
22.2	FC	38.00	Fiber Collimator	190 - 1250	#17-569	€545,90 Prix sur Quantité	5 In Stock
22.2	SMA	38.00	Fiber Collimator	190 - 1250	#17-567	€545,90 Prix sur Quantité	Contact
10.0	-	18.00	Refocusing Assembly	190 - 1250	#88-185	€331,66 Prix sur Quantité	Contact
10.0	-	18.00	Refocusing Assembly	350 - 2200	#88-182	€182,31 Prix sur Quantité	Contact
10.0	-	25.00	Refocusing Assembly	190 - 1250	#88-186	€331,66 Prix sur Quantité	2 In Stock
10.0	-	25.00	Refocusing Assembly	350 - 2200	#88-183	€182,31 Prix sur Quantité	Contact
22.2	-	38.00	Refocusing Assembly	190 - 1250	#17-573	€659,20 Prix sur Quantité	Contact
10.0	-	38.00	Refocusing Assembly	190 - 1250	#88-187	€331,66 Prix sur Quantité	2 In Stock

10.0	-	38.00	Refocusing Assembly	350 - 2200	#88-184	€182,31 Prix sur Quantité	4 In Stock
22.2	-	51.00	Refocusing Assembly	190 - 1250	#17-574	€659,20 Prix sur Quantité	7 In Stock
22.2	-	76.00	Refocusing Assembly	190 - 1250	#17-575	€659,20 Prix sur Quantité	Contact



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Téléphone: 1-800-363-1992 :

www.edmundoptics.com