

[Tous les Produits](#) / [Composants Optomécaniques](#) / [Ouvertures Optomécaniques](#) / [Sténopés et Diaphragmes à Fente](#)

Sténopés Noircis Acktar See More by [Acktar](#)



- Faible réflexion des UVE aux SWIR
- Traitement noir absorbant 99% de la lumière
- Taille d'ouverture comprise entre 20 et 1000 µm
- Versions montées et non montées disponibles

Spécifications

Propriétés physiques et mécaniques

Construction: Stainless Steel

Propriétés des matériaux

Absorption (%): 99

Informations techniques

Produits

Type	Diamètre Externe (mm)	Construction	Diamètre Fixe de l'Ouverture (µm)	Numéro de Stock	Prix	Achat
Unmounted	9.53	Stainless Steel	20	#15-386	€145,23 Prix sur Quantité	3 In Stock
Unmounted	9.53	Stainless Steel	25	#15-387	€145,23 Prix sur Quantité	2 In Stock
Unmounted	9.53	Stainless Steel	50	#12-166	€145,23 Prix sur Quantité	2 In Stock
Unmounted	9.53	Stainless Steel	75	#15-388	€145,23 Prix sur Quantité	2 In Stock
Unmounted	9.53	Stainless Steel	100	#12-167	€145,23 Prix sur Quantité	5 In Stock
Unmounted	9.53	Stainless Steel	150	#15-389	€145,23 Prix sur Quantité	4 In Stock
Unmounted	9.53	Stainless Steel	200	#12-168	€145,23 Prix sur Quantité	5 In Stock
Unmounted	9.53	Stainless Steel	300	#15-390	€145,23 Prix sur Quantité	2 In Stock
Unmounted	9.53	Stainless Steel	400	#15-391	€145,23 Prix sur Quantité	2 In Stock
Unmounted	9.53	Stainless Steel	500	#12-169	€145,23 Prix sur Quantité	4 In Stock
Unmounted	9.53	Stainless Steel	600	#15-392	€145,23 Prix sur Quantité	8 In Stock
Unmounted	9.53	Stainless Steel	800	#16-738	€145,23 Prix sur Quantité	4 In Stock
Unmounted	9.53	Stainless Steel	1000	#12-170	€145,23 Prix sur Quantité	5 In Stock
Mounted	12.7	Stainless Steel	25	#16-821	€155,53 Prix sur Quantité	3 In Stock
Mounted	12.7	Stainless Steel	50	#16-822	€155,53 Prix sur Quantité	20+ In Stock
Mounted	12.7	Stainless Steel	75	#16-823	€155,53 Prix sur Quantité	20+ In Stock
Mounted	12.7	Stainless Steel	100	#16-824	€155,53 Prix sur Quantité	2 In Stock

Mounted	12.7	Stainless Steel	150	#16-825	€155,53 Prix sur Quantité	1 In Stock
Mounted	12.7	Stainless Steel	200	#16-826	€155,53 Prix sur Quantité	3 In Stock
Mounted	12.7	Stainless Steel	300	#16-827	€155,53 Prix sur Quantité	4 In Stock
Mounted	12.7	Stainless Steel	500	#16-828	€155,53 Prix sur Quantité	5 In Stock
Mounted	12.7	Stainless Steel	1000	#16-829	€155,53 Prix sur Quantité	Contact
Mounted	25.0	Stainless Steel	20	#15-393	€155,53 Prix sur Quantité	4 In Stock
Mounted	25.0	Stainless Steel	25	#15-394	€155,53 Prix sur Quantité	5 In Stock
Mounted	25.0	Stainless Steel	50	#12-171	€155,53 Prix sur Quantité	5 In Stock
Mounted	25.0	Stainless Steel	75	#15-395	€155,53 Prix sur Quantité	3 In Stock
Mounted	25.0	Stainless Steel	100	#12-172	€155,53 Prix sur Quantité	6 In Stock
Mounted	25.0	Stainless Steel	150	#15-396	€155,53 Prix sur Quantité	4 In Stock
Mounted	25.0	Stainless Steel	200	#12-173	€155,53 Prix sur Quantité	5 In Stock
Mounted	25.0	Stainless Steel	300	#15-397	€155,53 Prix sur Quantité	2 In Stock
Mounted	25.0	Stainless Steel	400	#15-398	€155,53 Prix sur Quantité	3 In Stock
Mounted	25.0	Stainless Steel	500	#12-174	€155,53 Prix sur Quantité	2 In Stock
Mounted	25.0	Stainless Steel	600	#15-399	€155,53 Prix sur Quantité	2 In Stock
Mounted	25.0	Stainless Steel	800	#16-739	€155,53 Prix sur Quantité	2 In Stock
Mounted	25.0	Stainless Steel	1000	#12-175	€155,53 Prix sur Quantité	1 In Stock



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Téléphone: 1-800-363-1992 :

www.edmundoptics.com