


NOTES:

1. Substrate
2. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES
3. COATING (APPLY ACROSS COATING APERTURE)

S1: Ravg ≥ 95% @ 400 - 690nm @ 45° AOI  
 Tavg ≥ 90% @ 750 - 1200nm @ 45° AOI



S2: AR Coating: Ravg <1% @ 700 - 1150nm @ 45° AOI

FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING



FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. RoHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	<b>Edmund Optics®</b>			
SHAPE	PLANO	PLANO				
SURFACE FLATNESS	4 - 6λ	4 - 6λ	THIRD ANGLE PROJECTION	TITLE	20 x 20mm, 45° AOI, COLD MIRROR	
SURFACE QUALITY	80-50	80-50		DWG NO	64446	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm		SHEET 1 OF 1