



FOCAL LENGTH (EFL): 30 ±0,3  
 BACK FOCAL LENGTH (BFL): 28,31

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	39,22±0,039 CX	GLASS N-SF5 673/322	R	39,22±0,039 CX
Øe	24		Øe	24
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,49'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT    SCALE: NONE    λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm

**EO**® Edmund Optics®

TITLE 25mm Dia, x 30mm FL, Uncoated, Double-Convex Lens

DWG NO 63555

SHEET SIZE A4    SHEET 1 OF 1