


- NOTES:
- 1. SUBSTRATE: Fused Silica (Corning 7980)
 - 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: R(ABS) <0.25% @ 532nm
R(ABS) <0.10% 1064nm



DAMAGE threshold, pulsed:
5 J/cm² @ 532nm, 20ns, 20Hz
15 J/cm² @ 1064nm, 20ns, 20Hz
 - 3. FINE GRIND SURFACE
 - 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE FLATNESS	$\lambda/10$	$\lambda/10$
SURFACE QUALITY	10-5	10-5
CLEAR APERTURE	$\varnothing 68.58$	$\varnothing 68.58$
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	532, 1064nm, 76.2mm, Dual-Band AR Fused Silica Window
ALL DIMS IN	mm	DWG NO	20451
			SHEET 1 OF 1