



FOCAL LENGTH (EFL): 75 ± 0,75  
 BACK FOCAL LENGTH (BFL): 74,11

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	68,362±0,068 CX	GLASS FUSED SILICA 458/678	R	68,362±0,068 CX
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT  
 SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12mm Dia, x 75mm FL, Uncoated, UV Double-Convex Lens

DWG NO

48039

SHEET SIZE A4

SHEET 1 OF 1