

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

1 Identification

- **Product identifier**
- **Trade name:** MILBOND TYPE II PART B
- **Article number:** S12801-B
- **Application of the substance / the mixture** Laboratory chemicals
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
Electron Microscopy Sciences
1560 Industry Road
USA-Hatfield, PA 19440
Tel: 215-412-8400 Fax: 215-412-8450
email: sgkcck@aol.com
www.emsdiasum.com
- **Information department:** Product safety department
- **Emergency telephone number:**
ChemTrec 1-800-424-9300 Contract CCN7661
1-703-527-3887

2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS06 Skull and crossbones

Acute Tox. 2 H300 Fatal if swallowed.

Acute Tox. 2 H310 Fatal in contact with skin.

Acute Tox. 2 H330 Fatal if inhaled.



GHS08 Health hazard

Carc. 1A H350 May cause cancer.



GHS05 Corrosion

Eye Dam. 1 H318 Causes serious eye damage.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.

Skin Sens. 1 H317 May cause an allergic skin reaction.

- **Label elements**

- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 1)

· **Hazard pictograms**· **Signal word** *Danger*· **Hazard-determining components of labeling:**

(POLY(ACRYLONITRILE-CO-BUTADIENE), AMINE TERMINATED)

Versamid 140

Polyamide Resin

2,4,6-tris(dimethylaminomethyl)phenol

· **Hazard statements**

Fatal if swallowed, in contact with skin or if inhaled.

Causes skin irritation.

Causes serious eye damage.

May cause an allergic skin reaction.

May cause cancer.

· **Precautionary statements**

Obtain special instructions before use.

Do not handle until all safety precautions have been read and understood.

Do not breathe dust/fume/gas/mist/vapors/spray.

Do not get in eyes, on skin, or on clothing.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Use only outdoors or in a well-ventilated area.

Contaminated work clothing must not be allowed out of the workplace.

Wear protective gloves/protective clothing/eye protection/face protection.

[In case of inadequate ventilation] wear respiratory protection.

If swallowed: Immediately call a poison center/doctor.

Rinse mouth.

If on skin: Wash with plenty of water.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

IF exposed or concerned: Get medical advice/attention.

Specific treatment is urgent (see on this label).

Take off immediately all contaminated clothing and wash it before reuse.

If skin irritation or rash occurs: Get medical advice/attention.

Store in a well-ventilated place. Keep container tightly closed.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**· **NFPA ratings (scale 0 - 4)**

Health = 4

Fire = 1

Reactivity = 0

· **HMIS-ratings (scale 0 - 4)**

Health = 4

Fire = 1

Reactivity = 0

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 2)

- **Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Mixture of the substances listed below with nonhazardous additions.

- **Dangerous components:**

68683-29-4	(POLY(ACRYLONITRILE-CO-BUTADIENE), AMINE TERMINATED)	>50-≤100%
68410-23-1	Versamid 140 Polyamide Resin	>25-≤50%
90-72-2	2,4,6-tris(dimethylaminomethyl)phenol	≤2.5%

4 First-aid measures

- **Description of first aid measures**
- **General information:**
Immediately remove any clothing soiled by the product.
Remove breathing apparatus only after contaminated clothing have been completely removed.
In case of irregular breathing or respiratory arrest provide artificial respiration.
- **After inhalation:**
Supply fresh air or oxygen; call for doctor.
In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.
- **After swallowing:** Do not induce vomiting; immediately call for medical help.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:** Use fire fighting measures that suit the environment.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** Mouth respiratory protective device.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:**
Inform respective authorities in case of seepage into water course or sewage system.
Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 3)

Dispose contaminated material as waste according to item 13.

Ensure adequate ventilation.

· **Reference to other sections**

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

· **Protective Action Criteria for Chemicals**

· **PAC-1:**

68410-23-1	Versamid 140 Polyamide Resin	30 mg/m ³
90-72-2	2,4,6-tris(dimethylaminomethyl)phenol	6.5 mg/m ³

· **PAC-2:**

68410-23-1	Versamid 140 Polyamide Resin	330 mg/m ³
90-72-2	2,4,6-tris(dimethylaminomethyl)phenol	72 mg/m ³

· **PAC-3:**

68410-23-1	Versamid 140 Polyamide Resin	2,000 mg/m ³
90-72-2	2,4,6-tris(dimethylaminomethyl)phenol	430 mg/m ³

7 Handling and storage

· **Handling:**

· **Precautions for safe handling**

Ensure good ventilation/exhaustion at the workplace.

Open and handle receptacle with care.

Prevent formation of aerosols.

· **Information about protection against explosions and fires:** Keep respiratory protective device available.

· **Conditions for safe storage, including any incompatibilities**

· **Storage:**

· **Requirements to be met by storerooms and receptacles:** No special requirements.

· **Information about storage in one common storage facility:** Not required.

· **Further information about storage conditions:** Keep receptacle tightly sealed.

· **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

· **Additional information about design of technical systems:** No further data; see item 7.

· **Control parameters**

· **Components with limit values that require monitoring at the workplace:**

The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Immediately remove all soiled and contaminated clothing.

(Contd. on page 5)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 4)

Wash hands before breaks and at the end of work.

Store protective clothing separately.

Avoid contact with the skin.

Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**



Tightly sealed goggles

9 Physical and chemical properties

· **Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· Form:	Pasty
· Color:	Dark blue
· Odor:	Amine-like
· Odor threshold:	Not determined.

· pH-value:	Not determined.
--------------------	-----------------

· **Change in condition**

· Melting point/Melting range:	Undetermined.
· Boiling point/Boiling range:	160 °C (320 °F)

· Flash point:	115 °C (239 °F)
-----------------------	-----------------

· Flammability (solid, gaseous):	Not flammable.
---	----------------

· Decomposition temperature:	Not determined.
-------------------------------------	-----------------

· Auto igniting:	Product is not selfigniting.
-------------------------	------------------------------

· Danger of explosion:	Product does not present an explosion hazard.
-------------------------------	---

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 5)

· Explosion limits:	
· Lower:	Not determined.
· Upper:	Not determined.
· Vapor pressure:	Not determined.
· Density at 20 °C (68 °F):	0.944 g/cm ³ (7.87768 lbs/gal)
· Relative density	Not determined.
· Vapor density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with	
· Water:	Not miscible or difficult to mix.
· Partition coefficient (n-octanol/water):	Not determined.
· Viscosity:	
· Dynamic:	Not determined.
· Kinematic:	Not determined.
· Solvent content:	
· VOC content:	0.00 % 0.0 g/l / 0.00 lb/gal
· Solids content:	0.0 %
· Other information	No further relevant information available.

10 Stability and reactivity

- **Reactivity** No further relevant information available.
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** Irritant to skin and mucous membranes.
- **on the eye:** Strong irritant with the danger of severe eye injury.
- **Sensitization:** Sensitization possible through skin contact.
- **Additional toxicological information:**
The product shows the following dangers according to internally approved calculation methods for preparations:
Irritant
Very toxic
Danger through skin absorption.
Carcinogenic.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 6)

· **Carcinogenic categories**· **IARC (International Agency for Research on Cancer)**

None of the ingredients is listed.

· **NTP (National Toxicology Program)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety Health Administration)**

None of the ingredients is listed.

12 Ecological information

· **Toxicity**· **Aquatic toxicity:** No further relevant information available.· **Persistence and degradability** No further relevant information available.· **Behavior in environmental systems:**· **Bioaccumulative potential** No further relevant information available.· **Mobility in soil** No further relevant information available.· **Ecotoxical effects:**· **Remark:** Harmful to fish· **Additional ecological information:**· **General notes:**

Water hazard class 3 (Self-assessment): extremely hazardous for water

Do not allow product to reach ground water, water course or sewage system, even in small quantities.

Danger to drinking water if even extremely small quantities leak into the ground.

Harmful to aquatic organisms

· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.· **Other adverse effects** No further relevant information available.

13 Disposal considerations

· **Waste treatment methods**· **Recommendation:**

Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

· **Uncleaned packagings:**· **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

· **Packing group**· **DOT**

Void

· **Environmental hazards:**

Not applicable.

· **Special precautions for user**

Not applicable.

· **Stowage Category**

B

· **Stowage Code**

SW2 Clear of living quarters.

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 7)

- | | |
|--|--|
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · Transport/Additional information: | |
| · DOT | |
| · Quantity limitations | On passenger aircraft/rail: 5 L
On cargo aircraft only: 60 L |
| · IMDG | |
| · Limited quantities (LQ) | 100 ml |
| · Excepted quantities (EQ) | Code: E4
Maximum net quantity per inner packaging: 1 ml
Maximum net quantity per outer packaging: 500 ml |
| · UN "Model Regulation": | Void |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**

- **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

- **TSCA (Toxic Substances Control Act):**

All components have the value ACTIVE.

- **Hazardous Air Pollutants**

None of the ingredients is listed.

- **Proposition 65**

- **Chemicals known to cause cancer:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

- **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

(Contd. on page 9)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 8)

· **Hazard pictograms**· **Signal word** *Danger*· **Hazard-determining components of labeling:**

(POLY(ACRYLONITRILE-CO-BUTADIENE), AMINE TERMINATED)

Versamid 140

Polyamide Resin

2,4,6-tris(dimethylaminomethyl)phenol

· **Hazard statements**

Fatal if swallowed, in contact with skin or if inhaled.

Causes skin irritation.

Causes serious eye damage.

May cause an allergic skin reaction.

May cause cancer.

· **Precautionary statements**

Obtain special instructions before use.

Do not handle until all safety precautions have been read and understood.

Do not breathe dust/fume/gas/mist/vapors/spray.

Do not get in eyes, on skin, or on clothing.

Wash thoroughly after handling.

Do not eat, drink or smoke when using this product.

Use only outdoors or in a well-ventilated area.

Contaminated work clothing must not be allowed out of the workplace.

Wear protective gloves/protective clothing/eye protection/face protection.

[In case of inadequate ventilation] wear respiratory protection.

If swallowed: Immediately call a poison center/doctor.

Rinse mouth.

If on skin: Wash with plenty of water.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.

Continue rinsing.

IF exposed or concerned: Get medical advice/attention.

Specific treatment is urgent (see on this label).

Take off immediately all contaminated clothing and wash it before reuse.

If skin irritation or rash occurs: Get medical advice/attention.

Store in a well-ventilated place. Keep container tightly closed.

Store locked up.

Dispose of contents/container in accordance with local/regional/national/international regulations.

· **National regulations:**· **Information about limitation of use:**

Workers are not allowed to be exposed to the hazardous carcinogenic materials contained in this preparation.

Exceptions can be made by the authorities in certain cases.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

US

(Contd. on page 10)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/10/2021

Reviewed on 09/10/2021

Trade name: MILBOND TYPE II PART B

(Contd. of page 9)

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Date of preparation / last revision** 09/10/2021 / -

· **Abbreviations and acronyms:**

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

ACGIH: American Conference of Governmental Industrial Hygienists

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

NFPA: National Fire Protection Association (USA)

HMIS: Hazardous Materials Identification System (USA)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

NIOSH: National Institute for Occupational Safety

OSHA: Occupational Safety **Health**

TLV: Threshold Limit Value

PEL: Permissible Exposure Limit

REL: Recommended Exposure Limit

Acute Tox. 2: Acute toxicity – Category 2

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Skin Sens. 1: Skin sensitisation – Category 1

Carc. 1A: Carcinogenicity – Category 1A

US