




NOTES:

1. SUBSTRATE:
ZERODUR®
2. S2 TO BE PARALLEL TO S1 TO WITHIN <30 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1&S2:
Ravg >98% @ 400 - 750nm (0 - 45°) Ravg >99% @ 400 - 750nm (0°)

△ FINE GRIND SURFACE

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	COMMERCIAL POLISH
CLEAR APERTURE	Ø 9.00	N/A
SURFACE FLATNESS	λ/10	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

10mm Dia. 400 - 750nm Broadband λ/10
ZERODUR® Mirror

DWG NO

24021

SHEET
7 OF 18