




NOTES:

1. SUBSTRATE:
FUSED SILICA
2. PARALLELISM: 30 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: UV Enhanced Aluminum (250-700nm)
 R(avg) >85% @ 250 - 700nm
 R(avg) >89% @ 250 - 450nm
 S2: NONE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS
APPLY ACROSS CLEAR APERTURE


5. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20 - 10	COMMERICAL POLISH
SURFACE FLATNESS	$\lambda/20$ (PRE-COATING)	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

EO® **Edmund Optics**®

TITLE: 10mm Dia UV Enhanced Aluminum, $\lambda/20$ Mirror

DWG NO: 70285

SHEET 1 OF 8