





f' : $-50 \pm 0,5$

BACK FOCAL LENGTH (BFL): $-51,37$



LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 22,923 CV Øe 24 λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ 2,18' 5/ 40 - 20 6/ - P			GLASS Fused Silica 458/678 Nd: 1,458	R ∞ PL Øe 24 λ AR Rave(250nm - 700nm, 0°) ≤ 1,50% R(350nm - 450nm, 0°) ≤ 1,00% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P					
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110				ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION	EO[®] Edmund Optics[®]	
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
			TITLE	25mm Dia x -50mm FL, UV-VIS Coated, Plano-Concave Lens					
			DWG NO	71102		SHEET SIZE A4			
						SHEET 1 OF 1			