




NOTES:  
1. SUBSTRATE:  
BOROFLOAT®

2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1: DIELECTRIC MIRROR (400 - 750nm)  
R(avg) >99% @ 400 - 750nm @ 0 - 45° AOI  
R(avg) >99% @ 400 - 750nm @ 0° AOI

S2: NONE

3. FINE GRIND SURFACE

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE (%)	90	N/A
SURFACE QUALITY	60 - 40	COMMERCIAL POLISH
SURFACE FLATNESS	λ/4	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN

mm

**EO**® Edmund Optics®

TITLE

25mm Dia. 400 - 750nm Broadband λ/4 Mirror

DWG NO

70671

SHEET  
4 OF 5