


Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

586nm Fluorescence Bandpass Filter: 26nm FWHM OD >6.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

586nm Fluorescence Bandpass Filter OD >6.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

628nm Fluorescence Bandpass Filter: 38nm FWHM OD >6.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

628nm Fluorescence Bandpass Filter OD >6.0 Coating Performance FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

605nm TECHSPEC® Dichroic Filter FOR REFERENCE ONLY




COATING CURVE

Coating Curve

Edmund Optics Inc.
USA | Asia | Europe

605nm TECHSPEC® Dichroic Filter FOR REFERENCE ONLY



COATING CURVE