



NOTES:


- 1. SUBSTRATE: Polymer Film CP42HER
- 2. WAVELENGTH RANGE: 400 - 700 nm
- 3. POLARIZATION EFFICIENCY (%): >99.90
- 4. TRANSMISSION (%):
SINGLE: 42.00
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	300 x 300mm Right-Handed Plastic Circular Polarizer (CP42HER)	
ALL DIMS IN	mm	DWG NO	29451	SHEET 14 OF 50