

[Tous les Produits](#) / [Objectifs d'Imagerie](#) / [Objectifs Zoom & Objectifs à Grossissement Variable](#) / [Objectifs Zoom à Fort Grossissement et à Longue Distance de Travail](#)

## Objectifs Zoom 7X et 12,5X de Haute Précision



- Permettent d'obtenir un large éventail de grossissements
- Composants standard remplaçables pour une flexibilité maximale
- Options motorisées et in-line disponibles
- [Coffret d'Objectifs Zoom Haute Précision 7X et 12.5X](#) également disponible

## Informations techniques

## Produits

| Title                           | Remarque                    | Numéro de Stock         | Prix    | Achat        |
|---------------------------------|-----------------------------|-------------------------|---------|--------------|
| C-Mount Camera Adapter          | Camera Mount (One Required) | <a href="#">#89-860</a> | €66,50  | Contact      |
| F-Mount Camera Adapter          | Camera Mount (One Required) | <a href="#">#89-861</a> | €72,50  | 2 In Stock   |
| EOS Camera Adapter              | Camera Mount (One Required) | <a href="#">#89-862</a> | €96,00  | 1 In Stock   |
| K-Mount Camera Adapter          | Camera Mount (One Required) | <a href="#">#89-863</a> | €96,00  | 1 In Stock   |
| 4/3" Mount Camera Adapter       | Camera Mount (One Required) | <a href="#">#89-864</a> | €96,00  | 1 In Stock   |
| Micro 4/3" Mount Camera Adapter | Camera Mount (One Required) | <a href="#">#89-865</a> | €96,00  | 1 In Stock   |
| Sony Alpha Camera Adapter       | Camera Mount (One Required) | <a href="#">#89-866</a> | €96,00  | 2 In Stock   |
| 0.4X Camera Tube                | Camera Tube (One Required)  | <a href="#">#89-867</a> | €328,00 | 2 In Stock   |
| 0.5X Camera Tube                | Camera Tube (One Required)  | <a href="#">#89-868</a> | €328,00 | 20+ In Stock |
| 0.6X Camera Tube                | Camera Tube (One Required)  | <a href="#">#89-869</a> | €328,00 | 3 In Stock   |
| 0.8X Camera Tube                | Camera Tube (One Required)  | <a href="#">#89-870</a> | €328,00 | 1 In Stock   |
| 1.0X Camera Tube                | Camera Tube (One Required)  | <a href="#">#89-871</a> | €328,00 | 1 In Stock   |
| 0.8X Mini-Camera Tube           | Camera Tube (One Required)  | <a href="#">#89-872</a> | €835,00 | 1 In Stock   |
| 1.0X Mini-Camera Tube           | Camera Tube (One Required)  | <a href="#">#89-873</a> | €835,00 | 1 In Stock   |
| 1.5X Mini-Camera Tube           | Camera Tube (One Required)  | <a href="#">#89-874</a> | €835,00 | Contact      |
| 2.0X Mini-Camera Tube           | Camera Tube (One Required)  | <a href="#">#89-875</a> | €835,00 | 1 In Stock   |

|                                                                   |                                      |                         |           |             |
|-------------------------------------------------------------------|--------------------------------------|-------------------------|-----------|-------------|
| 2.5X Mini-Camera Tube                                             | Camera Tube (One Required)           | <a href="#">#89-876</a> | €835,00   | Contact     |
| 3.0X Mini-Camera Tube                                             | Camera Tube (One Required)           | <a href="#">#89-877</a> | €835,00   | Contact     |
| 7X Zoom Module, Manual                                            | Zoom Module (One Required)           | <a href="#">#89-878</a> | €915,00   | 2 In Stock  |
| 7X Zoom Module, Manual w/Detents                                  | Zoom Module (One Required)           | <a href="#">#89-879</a> | €1.030,00 | Contact     |
| 7X Zoom Module, Stepper Motorized                                 | Zoom Module (One Required)           | <a href="#">#89-880</a> | €2.010,00 | 4 In Stock  |
| 12.5X Zoom Module, Manual                                         | Zoom Module (One Required)           | <a href="#">#89-881</a> | €2.175,00 | 3 In Stock  |
| 12.5X Zoom Module, Manual w/Detents                               | Zoom Module (One Required)           | <a href="#">#89-882</a> | €2.290,00 | 4 In Stock  |
| 12.5X Zoom Module, Stepper Motorized                              | Zoom Module (One Required)           | <a href="#">#89-883</a> | €3.325,00 | Contact     |
| Fixed Aperture Set (Required if no Zoom Module)                   | Zoom Module (One Required)           | <a href="#">#89-884</a> | €109,00   | 1 In Stock  |
| Basic Lower Module, No Focus                                      | Lower Function Module (One Required) | <a href="#">#89-885</a> | €88,50    | 1 In Stock  |
| Lower Module w/15mm Manual Focus                                  | Lower Function Module (One Required) | <a href="#">#89-886</a> | €401,00   | 10 In Stock |
| Lower Module w/In-Line Illumination                               | Lower Function Module (One Required) | <a href="#">#89-888</a> | €339,00   | 3 In Stock  |
| Lower Module w/In-Line Illumination & Analyzer                    | Lower Function Module (One Required) | <a href="#">#89-889</a> | €795,00   | 1 In Stock  |
| Lower Module w/In-Line Illumination & 5mm Manual Focus            | Lower Function Module (One Required) | <a href="#">#89-890</a> | €750,00   | Contact     |
| Lower Module w/In-Line Illumination, Analyzer & 5mm Manual Focus  | Lower Function Module (One Required) | <a href="#">#89-891</a> | €1.830,00 | Contact     |
| Lower Module w/In-Line Illumination & 5mm Stepper Motorized Focus | Lower Function Module (One Required) | <a href="#">#89-892</a> | €1.830,00 | Contact     |

|                                                                      |                                            |                         |           |              |
|----------------------------------------------------------------------|--------------------------------------------|-------------------------|-----------|--------------|
| Lower Module w/In-Line,<br>Analyzer & 5mm Stepper<br>Motorized Focus | Lower Function<br>Module (One<br>Required) | <a href="#">#89-893</a> | €2.175,00 | 1 In Stock   |
| 0.4X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-894</a> | €260,00   | 1 In Stock   |
| 0.5X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-895</a> | €260,00   | 2 In Stock   |
| 0.67X Lower Lens                                                     | Lower Lens (One<br>Required)               | <a href="#">#89-896</a> | €260,00   | 1 In Stock   |
| 1.0X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-897</a> | €260,00   | 1 In Stock   |
| 1.25X Lower Lens                                                     | Lower Lens (One<br>Required)               | <a href="#">#89-898</a> | €260,00   | 1 In Stock   |
| 1.43X Lower Lens                                                     | Lower Lens (One<br>Required)               | <a href="#">#89-899</a> | €260,00   | 20+ In Stock |
| 1.67X Lower Lens                                                     | Lower Lens (One<br>Required)               | <a href="#">#89-900</a> | €260,00   | Contact      |
| 2.0X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-901</a> | €260,00   | 3 In Stock   |
| 3.0X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-902</a> | €339,00   | 1 In Stock   |
| 4.0X Lower Lens                                                      | Lower Lens (One<br>Required)               | <a href="#">#89-903</a> | €339,00   | Contact      |
| Mitutoyo Objective Adapter<br>(M26 x 36TPI)                          | Lower Lens (One<br>Required)               | <a href="#">#89-904</a> | €109,00   | Contact      |
| 50/50 Beamsplitter Cube                                              | Accessory<br>(Optional)                    | <a href="#">#89-905</a> | €915,00   | Contact      |
| Mirror Cube for Right Angle<br>Turn                                  | Accessory<br>(Optional)                    | <a href="#">#89-906</a> | €374,00   | Contact      |
| Mirror Cube Adapter for Use<br>with Lower Lenses                     | Accessory<br>(Optional)                    | <a href="#">#89-907</a> | €109,00   | 5 In Stock   |
| 25.4mm Filter Holder                                                 | Accessory<br>(Optional)                    | <a href="#">#89-908</a> | €88,50    | 3 In Stock   |
| Adjustable Iris                                                      | Accessory<br>(Optional)                    | <a href="#">#89-909</a> | €339,00   | 20+ In Stock |
| In-Line Mount                                                        | Accessory<br>(Optional)                    | <a href="#">#89-910</a> | €109,00   | 2 In Stock   |

|                                               |                         |                         |                                             |              |
|-----------------------------------------------|-------------------------|-------------------------|---------------------------------------------|--------------|
| Camera Tube Mounting Clamp                    | Accessory<br>(Optional) | <a href="#">#89-911</a> | €109,00                                     | 5 In Stock   |
| Adjustable Rail Mounting Stand                | Accessory<br>(Optional) | <a href="#">#89-912</a> | €2.750,00                                   | 1 In Stock   |
| Stepper Motor Controller                      | Accessory<br>(Optional) | <a href="#">#89-913</a> | €2.125,00                                   | Contact      |
| Controller Adapter for Lower Focus Modules    | Accessory<br>(Optional) | <a href="#">#89-914</a> | €281,00                                     | Contact      |
| Euro Style Cord                               | Accessory<br>(Optional) | <a href="#">#89-916</a> | €57,00                                      | Contact      |
| UK Style Cord                                 | Accessory<br>(Optional) | <a href="#">#89-917</a> | €57,00                                      | 1 In Stock   |
| Polarizer Illumination Accessory              | Accessory<br>(Optional) | <a href="#">#89-918</a> | €453,00                                     | 1 In Stock   |
| Fiber Optic Light Guide Adapter               | Accessory<br>(Optional) | <a href="#">#89-919</a> | €146,00                                     | 2 In Stock   |
| Fiber Optic Light Guide Adapter to 10mm       | Accessory<br>(Optional) | <a href="#">#89-920</a> | €72,50                                      | Contact      |
| In-line Port Right Angle Bend                 | Accessory<br>(Optional) | <a href="#">#89-921</a> | €374,00                                     | 1 In Stock   |
| Fiber Optic Ringlight Adapter                 | Accessory<br>(Optional) | <a href="#">#89-922</a> | €203,00                                     | 1 In Stock   |
| LED Ringlight Adapter                         | Accessory<br>(Optional) | <a href="#">#89-923</a> | €99,00                                      | 1 In Stock   |
| Mounting Clamp 76mm Diameter Microscope Stand | Accessory<br>(Optional) | <a href="#">#89-924</a> | €250,00                                     | 1 In Stock   |
| Mounting Clamp 82mm Diameter Microscope Stand | Accessory<br>(Optional) | <a href="#">#89-925</a> | €250,00                                     | 1 In Stock   |
| Mounting Clamp 83mm Diameter Microscope Stand | Accessory<br>(Optional) | <a href="#">#89-926</a> | €250,00                                     | 1 In Stock   |
| Mounting Clamp 84mm Diameter Microscope Stand | Accessory<br>(Optional) | <a href="#">#89-927</a> | €250,00                                     | 2 In Stock   |
| C-Mount Light Guide Mounting Adapter          | Accessory<br>(Optional) | <a href="#">#53-047</a> | €37,60<br><a href="#">Prix sur Quantité</a> | 20+ In Stock |



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Téléphone: 1-800-363-1992 :

[www.edmundoptics.com](http://www.edmundoptics.com)